



FS ротаметр для NaOH 30%; корпус: полисульфон d63

| Артикул        | d  | Шкала для NaOH<br>30% [l/h] | B   | E   | C   |
|----------------|----|-----------------------------|-----|-----|-----|
| FSIV025P3X0125 | 25 | 6 - 125                     | 394 | 350 | 356 |
| FSIV025P3X0725 | 25 | 35 - 725                    | 394 | 350 | 356 |
| FSIV032P3X0240 | 32 | 10 - 240                    | 400 | 350 | 356 |
| FSIV032P3X0420 | 32 | 20 - 420                    | 400 | 350 | 356 |
| FSIV032P3X0700 | 32 | 25 - 700                    | 400 | 350 | 356 |
| FSIV040P3X1150 | 40 | 50 - 1150                   | 408 | 350 | 356 |
| FSIV040P3X3200 | 40 | 200 - 3200                  | 408 | 350 | 356 |
| FSIV050P3X1700 | 50 | 100 - 1700                  | 418 | 350 | 356 |
| FSIV050P3X3700 | 50 | 200 - 3700                  | 418 | 350 | 356 |
| FSIV063P3X3000 | 63 | 100 - 3000                  | 432 | 350 | 356 |
| FSIV063P3X4700 | 63 | 250 - 4700                  | 432 | 350 | 356 |
| FSIV063P3X8500 | 63 | 500 - 8500                  | 432 | 350 | 356 |
| FSIV075P3X0012 | 75 | 1000 - 12000                | 444 | 350 | 356 |
| FSIV075P3X0165 | 75 | 1500 - 16500                | 444 | 350 | 356 |
| FSIV075P3X0043 | 75 | 8800 - 43000                | 444 | 350 | 356 |
| FSIV025P3M0054 | 25 | 2,5 - 54                    | 394 | 350 | 356 |
| FSIV025P3M0115 | 25 | 6 - 115                     | 394 | 350 | 356 |
| FSIV025P3M0235 | 25 | 11 - 235                    | 394 | 350 | 356 |
| FSIV032P3M0125 | 32 | 6 - 125                     | 400 | 350 | 356 |
| FSIV032P3M0200 | 32 | 10 - 200                    | 400 | 350 | 356 |
| FSIV032P3M0395 | 32 | 11 - 395                    | 400 | 350 | 356 |
| FSIV040P3M1700 | 40 | 100 - 1700                  | 408 | 350 | 356 |
| FSIV050P3M1500 | 50 | 100 - 1500                  | 418 | 350 | 356 |
| FSIV050P3M1600 | 50 | 120 - 1600                  | 418 | 350 | 356 |
| FSIV063P3M1700 | 63 | 60 - 1700                   | 432 | 350 | 356 |

|                |    |              |     |     |     |
|----------------|----|--------------|-----|-----|-----|
| FSIV063P3M2500 | 63 | 90 - 2500    | 432 | 350 | 356 |
| FSIV075P3M6000 | 75 | 670 - 6000   | 444 | 350 | 356 |
| FSIV025P3X0240 | 25 | 10 - 240     | 394 | 350 | 356 |
| FSIV025P3X0425 | 25 | 25 - 425     | 394 | 350 | 356 |
| FSIV025P3M0410 | 25 | 28 - 410     | 394 | 350 | 356 |
| FSIV032P3M0650 | 32 | 25 - 650     | 400 | 350 | 356 |
| FSIV032P3X1200 | 32 | 50 - 1200    | 400 | 350 | 356 |
| FSIV040P3M0600 | 40 | 25 - 600     | 408 | 350 | 356 |
| FSIV040P3M1100 | 40 | 55 - 1100    | 408 | 350 | 356 |
| FSIV040P3X1900 | 40 | 100 - 1900   | 408 | 350 | 356 |
| FSIV050P3M1000 | 50 | 50 - 1000    | 418 | 350 | 356 |
| FSIV050P3X3000 | 50 | 200 - 3000   | 418 | 350 | 356 |
| FSIV063P3M4000 | 63 | 200 - 4000   | 432 | 350 | 356 |
| FSIV075P3M7500 | 75 | 500 - 7500   | 444 | 350 | 356 |
| FSIV075P3M0022 | 75 | 4400 - 22000 | 444 | 350 | 356 |