



FC ротаметр для NaOH 30% корпус: полисульфон d16

Артикул	d	Шкала для NaOH 30% [l/h]	B	E	C
FCIV016P3X0085	16	0,5 - 8,5	199	165	171
FCIV016P3X0040	16	2,5 - 40	199	165	171
FCIV016P3X0120	16	10 - 120	199	165	171
FCIV016P3X0180	16	15 - 180	199	165	171
FCIV020P3X0375	20	2,5 - 37,5	208	170	176
FCIV020P3X0075	20	4 - 75	208	170	176
FCIV020P3X0140	20	5 - 140	208	170	176
FCIV020P3X0220	20	9 - 220	208	170	176
FCIV020P3X0360	20	24 - 360	208	170	176
FCIV025P3X0135	25	6 - 135	229	185	191
FCIV025P3X0230	25	13 - 230	229	185	191
FCIV025P3X0350	25	20 - 350	229	185	191
FCIV025P3X0600	25	25 - 600	229	185	191
FCIV032P3X0220	32	10 - 220	250	200	206
FCIV032P3X0350	32	20 - 350	250	200	206
FCIV032P3X0650	32	25 - 650	250	200	206
FCIV032P3X1000	32	50 - 1000	250	200	206
FCIV016P3M0003	16	0,25 - 3	199	165	171
FCIV016P3M0017	16	1 - 17	199	165	171
FCIV016P3M0045	16	2,5 - 45	199	165	171
FCIV016P3M0075	16	5 - 75	199	165	171
FCIV020P3M0125	20	1 - 12,5	208	170	176
FCIV020P3M0034	20	2 - 34	208	170	176
FCIV020P3M0063	20	2,5 - 63	208	170	176
FCIV020P3M0104	20	5 - 104	208	170	176

FCIV020P3M0170	20	10 - 170	208	170	176
FCIV025P3M0060	25	3,5 - 60	229	185	191
FCIV025P3M0092	25	5 - 92	229	185	191
FCIV025P3M0165	25	8 - 165	229	185	191
FCIV025P3M0380	25	20 - 380	229	185	191
FCIV032P3M0090	32	5 - 90	250	200	206
FCIV032P3M0150	32	7,5 - 150	250	200	206
FCIV032P3M0360	32	20 - 360	250	200	206
FCIV032P3M0650	32	25 - 650	250	200	206