




FC ротаметр для HCl 30% корпус: полисульфон d16

| Артикул        | d  | Шкала для HCl 30 - 33% [l/h] | B   | E   | C   |
|----------------|----|------------------------------|-----|-----|-----|
| FCIV016P2M0014 | 16 | 1,4 - 14                     | 199 | 165 | 171 |
| FCIV016P2M0018 | 16 | 2 - 18                       | 199 | 165 | 171 |
| FCIV016P2M0045 | 16 | 5 - 45                       | 199 | 165 | 171 |
| FCIV016P2M0090 | 16 | 10 - 90                      | 199 | 165 | 171 |
| FCIV016P2M0140 | 16 | 14 - 140                     | 199 | 165 | 171 |
| FCIV020P2M0023 | 20 | 2 - 23                       | 208 | 170 | 176 |
| FCIV020P2M0045 | 20 | 5 - 45                       | 208 | 170 | 176 |
| FCIV020P2M0090 | 20 | 10 - 90                      | 208 | 170 | 176 |
| FCIV020P2M0140 | 20 | 14 - 140                     | 208 | 170 | 176 |
| FCIV020P2M0185 | 20 | 19 - 185                     | 208 | 170 | 176 |
| FCIV020P2M0300 | 20 | 30 - 300                     | 208 | 170 | 176 |
| FCIV025P2M0075 | 25 | 7,5 - 75                     | 229 | 185 | 191 |
| FCIV025P2M0140 | 25 | 14 - 140                     | 229 | 185 | 191 |
| FCIV025P2M0185 | 25 | 19 - 185                     | 229 | 185 | 191 |
| FCIV025P2M0325 | 25 | 30 - 325                     | 229 | 185 | 191 |
| FCIV025P2M0600 | 25 | 45 - 600                     | 229 | 185 | 191 |
| FCIV032P2M0185 | 32 | 19 - 185                     | 250 | 200 | 206 |
| FCIV032P2M0280 | 32 | 28 - 280                     | 250 | 200 | 206 |

|                |    |          |     |     |     |
|----------------|----|----------|-----|-----|-----|
| FCIV032P2M0550 | 32 | 55 - 550 | 250 | 200 | 206 |
| FCIV032P2M0900 | 32 | 90 - 900 | 250 | 200 | 206 |