




FC ротаметр для NAOH 50% корпус: полисульфон d32

| Артикул        | d  | Шкала для NaOH<br>50% [l/h] | B   | E   | C   |
|----------------|----|-----------------------------|-----|-----|-----|
| FCIV016P5X0014 | 16 | 0.05-1.4                    | 199 | 165 | 171 |
| FCIV016P5X0008 | 16 | 0.5-8                       | 199 | 165 | 171 |
| FCIV016P5X0040 | 16 | 2.5-40                      | 199 | 165 | 171 |
| FCIV016P5X0055 | 16 | 4-55                        | 199 | 165 | 171 |
| FCIV020P5X0065 | 20 | 0.25-6.5                    | 208 | 170 | 176 |
| FCIV020P5X0015 | 20 | 1-15                        | 208 | 170 | 176 |
| FCIV020P5X0036 | 20 | 2-36                        | 208 | 170 | 176 |
| FCIV020P5X0075 | 20 | 4-75                        | 208 | 170 | 176 |
| FCIV020P5X0140 | 20 | 6-140                       | 208 | 170 | 176 |
| FCIV025P5X0030 | 25 | 2.5-30                      | 229 | 185 | 191 |
| FCIV025P5X0065 | 25 | 3-65                        | 229 | 185 | 191 |
| FCIV025P5X0135 | 25 | 3.5-135                     | 229 | 185 | 191 |
| FCIV025P5X0320 | 25 | 20-320                      | 229 | 185 | 191 |
| FCIV032P5X0055 | 32 | 2.5-55                      | 250 | 200 | 206 |
| FCIV032P5X0125 | 32 | 5-125                       | 250 | 200 | 206 |
| FCIV032P5X0300 | 32 | 20-300                      | 250 | 200 | 206 |
| FCIV032P5X0600 | 32 | 25-600                      | 250 | 200 | 206 |
| FCIV016P5M0005 | 16 | 0,025 - 0,5                 | 199 | 165 | 171 |

|                |    |             |     |     |     |
|----------------|----|-------------|-----|-----|-----|
| FCIV016P5M0275 | 16 | 0,25 - 2,75 | 199 | 165 | 171 |
| FCIV016P5M0009 | 16 | 0,5 - 9     | 199 | 165 | 171 |
| FCIV016P5M0021 | 16 | 1 - 21      | 199 | 165 | 171 |
| FCIV020P5M0002 | 20 | 0,1 - 2     | 208 | 170 | 176 |
| FCIV020P5M0055 | 20 | 0,25 - 5,5  | 208 | 170 | 176 |
| FCIV020P5M0125 | 20 | 0,5 - 12,5  | 208 | 170 | 176 |
| FCIV020P5M0255 | 20 | 2 - 25,5    | 208 | 170 | 176 |
| FCIV020P5M0475 | 20 | 2,5 - 47,5  | 208 | 170 | 176 |
| FCIV025P5M0010 | 25 | 1 - 10      | 229 | 185 | 191 |
| FCIV025P5M0019 | 25 | 1 - 19      | 229 | 185 | 191 |
| FCIV025P5M0130 | 25 | 4 - 130     | 229 | 185 | 191 |
| FCIV032P5M0015 | 32 | 1 - 15      | 250 | 200 | 206 |
| FCIV032P5M0040 | 32 | 2 - 40      | 250 | 200 | 206 |
| FCIV032P5M0110 | 32 | 5 - 110     | 250 | 200 | 206 |
| FCIV032P5M0260 | 32 | 10 - 260    | 250 | 200 | 206 |
| FCIV025P5M0045 | 25 | 2 - 45      | 229 | 185 | 191 |