



FS ротаметр для NaOH 50%; корпус: полисульфон d50

| Артикул        | d  | Шкала для NaOH<br>50% [l/h] | B   | E   | C   |
|----------------|----|-----------------------------|-----|-----|-----|
| FSIV063P5X6000 | 63 | 250 - 6000                  | 432 | 350 | 356 |
| FSIV050P5M0425 | 50 | 25 - 425                    | 418 | 350 | 356 |
| FSIV025P5X0350 | 25 | 15 - 350                    | 394 | 350 | 356 |
| FSIV032P5X0145 | 32 | 5 - 145                     | 400 | 350 | 356 |
| FSIV075P5X0125 | 75 | 500 - 12500                 | 444 | 350 | 356 |
| FSIV032P5M0260 | 32 | 10 - 260                    | 400 | 350 | 356 |
| FSIV025P5M0095 | 25 | 0,5 - 9,5                   | 394 | 350 | 356 |
| FSIV063P5X3100 | 63 | 100 - 3100                  | 432 | 350 | 356 |
| FSIV025P5X0070 | 25 | 2,5 - 70                    | 394 | 350 | 356 |
| FSIV040P5X0550 | 40 | 25 - 550                    | 408 | 350 | 356 |
| FSIV050P5X1900 | 50 | 50 - 1900                   | 418 | 350 | 356 |
| FSIV075P5X9000 | 75 | 250 - 9000                  | 444 | 350 | 356 |
| FSIV040P5M0500 | 40 | 20 - 500                    | 408 | 350 | 356 |
| FSIV032P5M0020 | 32 | 1 - 20                      | 400 | 350 | 356 |
| FSIV050P5M0950 | 50 | 40 - 950                    | 418 | 350 | 356 |
| FSIV063P5M2500 | 63 | 80 - 2500                   | 432 | 350 | 356 |
| FSIV075P5M3800 | 75 | 330 - 3800                  | 444 | 350 | 356 |
| FSIV075P5M0020 | 75 | 4100 - 20000                | 444 | 350 | 356 |

|                |    |              |     |     |     |
|----------------|----|--------------|-----|-----|-----|
| FSIV032P5X0330 | 32 | 10 - 330     | 400 | 350 | 356 |
| FSIV075P5M5200 | 75 | 170 - 5200   | 444 | 350 | 356 |
| FSIV050P5M0800 | 50 | 25 - 800     | 418 | 350 | 356 |
| FSIV025P5X0027 | 25 | 1 - 27       | 394 | 350 | 356 |
| FSIV025P5X0170 | 25 | 5 - 170      | 394 | 350 | 356 |
| FSIV032P5X0065 | 32 | 2,5 - 65     | 400 | 350 | 356 |
| FSIV032P5X0675 | 32 | 25 - 675     | 400 | 350 | 356 |
| FSIV040P5X1100 | 40 | 50 - 1100    | 408 | 350 | 356 |
| FSIV040P5X2000 | 40 | 100 - 2000   | 408 | 350 | 356 |
| FSIV050P5X1000 | 50 | 50 - 1000    | 418 | 350 | 356 |
| FSIV050P5X2500 | 50 | 100 - 2500   | 418 | 350 | 356 |
| FSIV063P5X1800 | 63 | 50 - 1800    | 432 | 350 | 356 |
| FSIV075P5X0040 | 75 | 8200 - 40000 | 444 | 350 | 356 |
| FSIV025P5M0023 | 25 | 1,5 - 23     | 394 | 350 | 356 |
| FSIV025P5M0065 | 25 | 3 - 65       | 394 | 350 | 356 |
| FSIV025P5M0145 | 25 | 7 - 145      | 394 | 350 | 356 |
| FSIV032P5M0050 | 32 | 2,5 - 50     | 400 | 350 | 356 |
| FSIV032P5M0130 | 32 | 5,5 - 130    | 400 | 350 | 356 |
| FSIV040P5M0950 | 40 | 25 - 950     | 408 | 350 | 356 |
| FSIV063P5M0800 | 63 | 30 - 800     | 432 | 350 | 356 |
| FSIV063P5M1400 | 63 | 40 - 1400    | 432 | 350 | 356 |
| FSIV040P5M0200 | 40 | 10 - 200     | 408 | 350 | 356 |