



FC ротаметр для NaOH 30% корпус: полисульфон d25

| Артикул        | d  | Шкала для NaOH 30% [l/h] | B   | E   | C   |
|----------------|----|--------------------------|-----|-----|-----|
| FCIV020P3X0375 | 20 | 2,5 - 37,5               | 208 | 170 | 176 |
| FCIV032P3X0220 | 32 | 10 - 220                 | 250 | 200 | 206 |
| FCIV016P3X0120 | 16 | 10 - 120                 | 199 | 165 | 171 |
| FCIV020P3X0075 | 20 | 4 - 75                   | 208 | 170 | 176 |
| FCIV032P3X0650 | 32 | 25 - 650                 | 250 | 200 | 206 |
| FCIV016P3M0075 | 16 | 5 - 75                   | 199 | 165 | 171 |
| FCIV020P3M0063 | 20 | 2,5 - 63                 | 208 | 170 | 176 |
| FCIV025P3M0092 | 25 | 5 - 92                   | 229 | 185 | 191 |
| FCIV016P3X0040 | 16 | 2,5 - 40                 | 199 | 165 | 171 |
| FCIV032P3X0350 | 32 | 20 - 350                 | 250 | 200 | 206 |
| FCIV016P3M0003 | 16 | 0,25 - 3                 | 199 | 165 | 171 |
| FCIV032P3M0360 | 32 | 20 - 360                 | 250 | 200 | 206 |
| FCIV020P3X0220 | 20 | 9 - 220                  | 208 | 170 | 176 |
| FCIV032P3M0090 | 32 | 5 - 90                   | 250 | 200 | 206 |
| FCIV016P3X0180 | 16 | 15 - 180                 | 199 | 165 | 171 |
| FCIV020P3X0360 | 20 | 24 - 360                 | 208 | 170 | 176 |
| FCIV025P3X0135 | 25 | 6 - 135                  | 229 | 185 | 191 |
| FCIV025P3X0230 | 25 | 13 - 230                 | 229 | 185 | 191 |
| FCIV032P3X1000 | 32 | 50 - 1000                | 250 | 200 | 206 |
| FCIV016P3M0017 | 16 | 1 - 17                   | 199 | 165 | 171 |
| FCIV020P3M0125 | 20 | 1 - 12,5                 | 208 | 170 | 176 |
| FCIV020P3M0034 | 20 | 2 - 34                   | 208 | 170 | 176 |
| FCIV016P3X0085 | 16 | 0,5 - 8,5                | 199 | 165 | 171 |
| FCIV020P3X0140 | 20 | 5 - 140                  | 208 | 170 | 176 |
| FCIV025P3X0350 | 25 | 20 - 350                 | 229 | 185 | 191 |

|                |    |           |     |     |     |
|----------------|----|-----------|-----|-----|-----|
| FCIV025P3X0600 | 25 | 25 - 600  | 229 | 185 | 191 |
| FCIV016P3M0045 | 16 | 2,5 - 45  | 199 | 165 | 171 |
| FCIV020P3M0104 | 20 | 5 - 104   | 208 | 170 | 176 |
| FCIV020P3M0170 | 20 | 10 - 170  | 208 | 170 | 176 |
| FCIV025P3M0165 | 25 | 8 - 165   | 229 | 185 | 191 |
| FCIV025P3M0380 | 25 | 20 - 380  | 229 | 185 | 191 |
| FCIV032P3M0150 | 32 | 7,5 - 150 | 250 | 200 | 206 |
| FCIV032P3M0650 | 32 | 25 - 650  | 250 | 200 | 206 |
| FCIV025P3M0060 | 25 | 3,5 - 60  | 229 | 185 | 191 |